

UNITRONIC® LiYY (TP) BK

Data cable with DIN 47100 colour code and twisted pairs, Black/ UV resistant/ Outdoor use

UNITRONIC® - Low-frequency PVC data cable, DIN 47100 colour code, Twisted Pairs, Flame retardant, Instrumentation Control Automation, Outdoor use (black sheath)

Info

The classic for multi-functional use - in black

TP = twisted pair

UV resistant/ Outdoor use



Suitable for outdoor use



UV-resistant

Benefits

Decoupling of circuits by means of

twisted-pair (TP) design (crosstalk effects)

Outdoor use according to European standards

Application range

Dry or damp rooms

Outdoor use according to European standards

Product features

Twisted in pairs to reduce decoupling. As a result, additional screening is often not required.

Flame-retardant according IEC 60332-1-2

UV resistant according to EN 50525-1

Ozone-resistant

Norm references / Approvals

Based on VDE 0812

Product Make-up

Fine-wire strand made of bare copper wires

Core insulation made of PVC

TP structure

Outer sheath made of PVC

Outer sheath colour: black

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000104

ETIM 5.0 Class-Description: Control cable

Last Update (29.05.2021)

©2021 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

UNITRONIC® LiYY (TP) BK

Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	DIN 47100, refer to Appendix T9
Mutual capacitance:	Approx. 120 nF/km
Inductivity:	approx. 0.65 mH/km
Conductor stranding:	Fine copper wire strands
Minimum bending radius:	Occasional flexing: 10 x outer diameter Fixed installation: 4 x Outer diameter
Temperature range:	Occasional flexing: -5°C to +70°C Fixed installation: -40°C to +80°C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil \leq 30 kg or \leq 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UNITRONIC® LIYY (TP) BK

Article number	Number of pairs and conductor cross section (mm ²)	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1030400	2 x 2 x 0.14	4.5	5.4	25
1030401	3 x 2 x 0.14	5	8	32
1030402	4 x 2 x 0.14	5.6	10.7	38
1030403	5 x 2 x 0.14	5.8	13.4	45
1030404	6 x 2 x 0.14	6.3	16.1	51
1030405	10 x 2 x 0.14	8.1	26.9	77
1030407	16 x 2 x 0.14	9.2	43	110
1030408	2 x 2 x 0.25	5.7	9.6	38
1030409	3 x 2 x 0.25	6.3	14.4	48
1030410	4 x 2 x 0.25	7	19.2	59
1030411	6 x 2 x 0.25	7.9	28.8	80
1030412	8 x 2 x 0.25	9.3	38.4	98
1030413	2 x 2 x 0.5	7.3	19.2	72
1030414	3 x 2 x 0.5	8.1	28.8	83
1030415	4 x 2 x 0.5	8.8	38.4	115
1030416	8 x 2 x 0.5	12.3	76.8	206
1030417	10 x 2 x 0.5	13.3	96	247

Last Update (29.05.2021)

©2021 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16